

Lok-it! Power Series (PS)

Special Lok-it! lamps with enhanced performance features, including Brilliant and Blue options



Areas of application

- Concert Lighting
- Club & Disco
- Stage & Theatre
- Studio, TV, & Film
- Architecture & Architainment

Product features and benefits

- Compact design and short arc gap allows for smaller and brighter fixures
- Fast lamp replacement with one-touch rotate and lock base and socket design
- Robust design with eXtreme Seal (XS) technology, allowing up to 450°C at the pinch seal
- Consistent lumen output over the life of the lamp
- Improved ceramic base allows high voltage up to 35kV
- Higher luminous efficacy than conventional HID lamps provides higher fixture efficiency
- Power series offers enhanced performance features and versatility, including BRILLIANT lamps with high CRI and BLUE lamps that offer 7500K for bright white light





Product family datasheet

Technical data

	General Product Information				
Product description	Product number (Americas)	Product name (Americas)	Family brand	Global order reference	
Lok-it! 1000/PS	55022	LOKIT 1000/PS 10/CS 1/SKU	Lok-it!	Lok-it! 1000/PS	
Lok-it! 1000/PS Blue	55025	LOKIT 1000/PS BLUE 10/CS 1/SKU	Lok-it!	Lok-it! 1000/PS Blue	
Lok-it! 1000/PS Brilliant	55024	LOKIT 1000/PS BRILLIANT 10/CS 1/SKU	Lok-it!	Lok-it! 1000/PS Brilliant	
Lok-it! 1400/PS Brilliant	55026	LOKIT 1400/PS BRILLIANT 10/CS 1/SKU	Lok-it!	Lok-it! 1400/PS Brilliant	
Lok-it! 1700/PS	55027	LOKIT 1700/PS 10/CS 1/SKU	Lok-it!	Lok-it! 1700/PS	
Lok-it! 2000/PS	4062172169561	LOK-IT! 2000W/PS BRILLIANT 10/CS 1/SKU	Lok-it!	Lok-it! 2000/PS	
	Electrical Data		Photometric Data		
Product description	Nominal wattage	Nominal voltage	Nominal luminous	Color temperature	
Lok-it! 1000/PS	1000 W	85.0 V	85000 lm	6000 K	
Lok-it! 1000/PS Blue	1000 W	85.0 V	75000 lm	7200 K	
Lok-it! 1000/PS Brilliant	1000 W	85.0 V	82000 lm	6000 K	
Lok-it! 1400/PS Brilliant	1400 W	95.5 V	118000 lm	6000 K	
Lok-it! 1700/PS	1700 W	84.5 V	135000 lm	6000 K	
Lok-it! 2000/PS	2000 W	108 V	165000 lm	6000 K	
	Physical Attributes & Dimensions				
	Physical Attributes &	Dimensions			
Product description	Physical Attributes & Electrode gap (cold)	Lamp base	Diameter	Diameter (in)	
Product description Lok-it! 1000/PS	,		Diameter 28.0 mm	Diameter (in) 0.827 in	
•	Electrode gap (cold)				
Lok-it! 1000/PS	Electrode gap (cold) 5.5 mm	Lamp base	28.0 mm		
Lok-it! 1000/PS Lok-it! 1000/PS Blue	Electrode gap (cold) 5.5 mm 5.5 mm	Lamp base - -	28.0 mm 28.0 mm		
Lok-it! 1000/PS Lok-it! 1000/PS Blue Lok-it! 1000/PS Brilliant	Electrode gap (cold) 5.5 mm 5.5 mm 5.5 mm	Lamp base	28.0 mm 28.0 mm 28.0 mm		

		Operating Conditions	Lifetime Data
Length	Product weight	Burning position	Nominal lifetime
112.5 mm	57.00 g	Any	950 hr
112.5 mm	57.00 g		750 hr
112.5 mm	57.00 g		750 hr
120.0 mm	60.00 g		750 hr
121.0 mm	60.00 g		750 hr
121.0 mm	60.00 g		750 hr
	112.5 mm 112.5 mm 112.5 mm 120.0 mm 121.0 mm	112.5 mm 57.00 g 112.5 mm 57.00 g 112.5 mm 57.00 g 112.5 mm 60.00 g 121.0 mm 60.00 g	Length Product weight Burning position 112.5 mm 57.00 g Any 112.5 mm 57.00 g 112.5 mm 57.00 g 120.0 mm 60.00 g 121.0 mm 60.00 g

Product family datasheet

Environmental & Regulatory Information
Information according Art. 33 of EU Regulation (EC) 1907/2006
(REACh)

	(KLACII)		
Product description	Primary article identifier	Declaration no. in SCIP database	Candidate list substance 1
Lok-it! 1000/PS	4052899382947 4008321788368 4052899965157	No declarable substances contained	No declarable substances contained
Lok-it! 1000/PS Blue	4052899965171	No declarable substances contained	No declarable substances contained
Lok-it! 1000/PS Brilliant	4052899568266 4052899965164	No declarable substances contained	No declarable substances contained
Lok-it! 1400/PS Brilliant	4052899965195	No declarable substances contained	No declarable substances contained
Lok-it! 1700/PS	4052899965201	No declarable substances contained	No declarable substances contained
Lok-it! 2000/PS	4062172169561	No declarable substances contained	No declarable substances contained

Product family datasheet

Safety advice

Because of their high luminance, UV radiation and high internal pressure during operation, Lok-it! lamps may only be operated in enclosed lamp casings specially constructed for the purpose. Appropriate filters must ensure that UV radiation is reduced to an acceptable level. Mercury is released if the lamp breaks. Special safety precautions must be taken. Information on safety and handling is available on request or can be found in the leaflet included with the lamp or in the operating instructions.

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.